



HICHROM

Chromatography Columns and Supplies

**LC CONSUMABLES
AND ACCESSORIES
HPLC Detector Lamps
& Column Storage**

Catalogue 9

Hichrom Limited

**1 The Markham Centre, Station Road
Theale, Reading, Berks, RG7 4PE, UK**

Tel: +44 (0)118 930 3660 Fax: +44 (0)118 932 3484

Email: sales@hichrom.co.uk www.hichrom.co.uk

HPLC DETECTOR LAMPS

- All lamps from Quality Assured manufacturers
- All lamps tested to guarantee performance

In addition to supplying a range of Agilent UV detector and spectrophotometer lamps, Hichrom offers a range of replacement lamps for Agilent and many other commonly used HPLC UV detectors. Please enquire for instrument lamps not listed.



Agilent UV Detector and Spectrophotometer Lamps

Detector Type	Configuration	Lamp Type	Catalogue No.	Price
VWD	G1314D/E/F	Long life deuterium with RFID tag	G1314-60101	
	G1314A/B/C, 1120, 1220 Infinity LC	Long life deuterium	G1314-60100	
	G1315C/D, G1365C/D	Long life deuterium with RFID tag	2140-0820	
DAD/MWD	G1315A/B, G1365A/B	Long life deuterium	2140-0813	
	G1315A/B, G1365A/B	Long life deuterium	5182-1530	
	G1315A/B/C/D, G1365A/B/C/D	Tungsten	G1103-60001	

Replacement Lamps for Other Detectors and Spectrophotometers

Instrument Manufacturer ¹	Model ²	Catalogue No.	Price
Agilent	G1315A/B, G1365A/B, G1314A/B/C	LAG-1001	
		LAG-1002	
Applied Biosystems	757, 759, 783A, 785A, 980 + others	LAP-1001	
Cecil Instruments	1000, 1070, 2000, 5000 and 6000 Series + others	LCE-1001	
Gilson	115, 116, 117, 118, 119, 151, 152, 153, 155	LGI-1001	
		LKA-1001	
Knauer	8700, 9700 Wellchrom Series	LKA-1001	
		LKA-1002	
Perkin Elmer	Int. 2000, Int. 4000, LC55, LC55B, LC65T, LC75, LC85, LC135 Lambda Series	LPE-1001	
		LPE-1007	
Shimadzu	LC3, LC4A, LC6A UV- Series	LSH-1001	
		LSH-1004	
Varian	Spectra A10, Spectra A20, Spectra A30, Spectra A40, 75 Series	LVA-1002	
Waters	480, 481, 480LC, 481LC, Lambda Max 484	LWA-1001	
		LWA-1002	

¹ Lamps for other manufacturers' models also supplied

² Lamps for other models also supplied

HPLC COLUMN STORAGE SYSTEM

- Simple and compact stackable units
- Prevents HPLC column damage
- Enables easy identification
- Holds all end-fitting types

The HPLC Column Storage System is a 100% steel cabinet, offering a simple and compact method for preventing columns getting lost or damaged. A single drawer can store up to 12 x 12.5cm columns, or a combination of short columns, guard columns and analytical columns. The cabinet can hold all columns up to 300mm in length in flexible foam inserts. This keeps the columns secure, eliminating the possibility of damaging shocks to the columns. An optional moulded 6 position tray is available for easy storage of HPLC tools and fittings.

Specifications and Ordering Information

	Column Storage 30	Column Storage 60
Capacity	30 HPLC columns	60 HPLC columns
Dimensions (W x H x D)	279 x 325 x 408mm	279 x 670 x 408mm
Weight	12kg packed, 10.5kg unpacked	22kg packed, 20kg unpacked
Catalogue Number	ColStor30	ColStor60
Price		

