



# Safety Data Sheet

## Barium Sulfate

---

### 1. PRODUCT AND COMPANY IDENTIFICATION

---

**Product Name:** Barium Sulfate

**Synonyms/Generic Names:** Baryte

**SDS Number:** 86.00

**Product Use:** For Educational Use Only

**Manufacturer:** Columbus Chemical Industries, Inc.  
N4335 Temkin Rd.  
Columbus, WI. 53925

**For More Information Contact:** Ward's Science  
5100 West Henrietta Rd.  
PO Box 92912-9012  
Rochester, NY 14692  
(800) 962-2660 (Monday-Friday 7:30-7:00 Eastern Time)

**In Case of Emergency Call:** CHEMTREC - 800-424-9300 or 703-527-3887 (24 Hours/Day, 7 Days/Week)

---

### 2. HAZARDS IDENTIFICATION

---

**OSHA Hazards:** Target organ effect

**Target Organs:** Lungs

**Signal Words:** None

**Pictograms:** None

**GHS Classification:**

Acute aquatic toxicity	Category 3
------------------------	------------

**GHS Label Elements, including precautionary statements:**

**Hazard Statements:**

H402	Harmful to aquatic life.
------	--------------------------

**Precautionary Statements:**

P273	Avoid release to the environment.
------	-----------------------------------

**Potential Health Effects**

<b>Eyes</b>	May cause eye irritation.
<b>Inhalation</b>	May be harmful if inhaled. Causes respiratory tract irritation.
<b>Skin</b>	May be harmful if absorbed through skin. Causes skin irritation.
<b>Ingestion</b>	May be harmful if swallowed.

**NFPA Ratings**

Health	1
Flammability	0
Reactivity	0
Specific hazard	Not Available

**HMIS Ratings**

Health	1
Fire	0
Reactivity	0
Personal	E

**3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	Weight %	CAS #	EINECS# / ELINCS#	Formula	Molecular Weight
Barium Sulfate	100	7727-43-7	231-784-4	BaSO <sub>4</sub>	233.39 g/mol

**4. FIRST-AID MEASURES**

<b>Eyes</b>	In case of eye contact, rinse with plenty of water and seek medical attention if necessary.
<b>Inhalation</b>	Move casualty to fresh air and keep at rest. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Get medical attention.
<b>Skin</b>	Flush with plenty of water and wash using soap. Get medical attention if necessary.
<b>Ingestion</b>	<b>Do Not Induce Vomiting!</b> Never give anything by mouth to an unconscious person. If conscious, wash out mouth with water. Get medical attention if necessary.

**5. FIRE-FIGHTING MEASURES**

<b>Suitable (and unsuitable) extinguishing media</b>	Product is not flammable. Use appropriate media for adjacent fire. Cool containers with water.
<b>Special protective equipment and precautions for firefighters</b>	Wear self-contained, approved breathing apparatus and full protective clothing, including eye protection and boots.
<b>Specific hazards arising from the chemical</b>	Emits toxic fumes (sulfur oxides, barium oxides) under fire conditions. See also Stability and Reactivity section.

**6. ACCIDENTAL RELEASE MEASURES**

<b>Personal precautions, protective equipment and emergency procedures</b>	See section 8 for recommendations on the use of personal protective equipment.
<b>Environmental precautions</b>	Prevent spillage from entering drains. Any release to the environment may be subject to federal/national or local reporting requirements.
<b>Methods and materials for containment and cleaning up</b>	Sweep up and place in a suitable container for disposal. Clean surfaces thoroughly with water to remove residual contamination. Dispose of all waste and cleanup materials in accordance with regulations.

**7. HANDLING AND STORAGE****Precautions for safe handling**

See section 8 for recommendations on the use of personal protective equipment. Use with adequate ventilation and avoid breathing in dust. Wash thoroughly after using. Keep container closed when not in use.

**Conditions for safe storage, including any incompatibilities**

Store in cool, dry well ventilated area. Keep away from incompatible materials (see section 10 for incompatibilities).

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

### Occupational exposure controls:

Component	Exposure Limits	Basis	Entity
Barium Sulfate	10 mg/m <sup>3</sup>	TLV	USA ACGIH
	10 mg/m <sup>3</sup>	PEL	USA OSHA
	5 mg/m <sup>3</sup>	REL	USA NIOSH

TWA: Time Weighted Average over 8 hours of work.

TLV: Threshold Limit Value over 8 hours of work.

REL: Recommended Exposure Limit

PEL: Permissible Exposure Limit

STEL: Short Term Exposure Limit during x minutes.

IDLH: Immediately Dangerous to Life or Health

WEEL: Workplace Environmental Exposure Levels

CEIL: Ceiling

### Personal Protection

<b>Eyes</b>	Wear chemical safety glasses or goggles.
<b>Inhalation</b>	Provide local exhaust, preferably mechanical. If exposure levels are excessive, use an approved respirator.
<b>Skin</b>	Wear nitrile or rubber gloves, apron or lab coat. The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.
<b>Other</b>	Not Available

### Other Recommendations

Provide eyewash stations, quick-drench showers and washing facilities accessible to areas of use and handling.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance (physical state, color, etc.)	White powder.
Odor	Not Available
Odor threshold	Not Available
pH	Not Available
Melting point/freezing point	1580°C (2876°F)
Initial boiling point and boiling range	1600°C (2912°F)
Flash point	Not Available
Evaporation rate	Not Available
Flammability (solid, gas)	Not Available
Upper/lower flammability or explosive limit	Not Available
Vapor pressure	Not Available
Vapor density	Not Available
Relative density	4.5 g/cm <sup>3</sup>
Solubility (ies)	Very slightly soluble in water.
Partition coefficient: n-octanol/water	Not Available
Auto-ignition temperature	Not Available
Decomposition temperature	Not Available

---

## 10. STABILITY AND REACTIVITY

---

<b>Chemical Stability</b>	Stable
<b>Possibility of Hazardous Reactions</b>	Will not occur.
<b>Conditions to Avoid</b>	Not Available
<b>Incompatible Materials</b>	Aluminum, phosphorus.
<b>Hazardous Decomposition Products</b>	Sulfur oxides, barium oxide.

---

## 11. TOXICOLOGICAL INFORMATION

---

### Acute Toxicity

<b>Skin</b>	Not Available
<b>Eyes</b>	Not Available
<b>Respiratory</b>	Not Available
<b>Ingestion</b>	Not Available

### Carcinogenicity

<b>IARC</b>	No components of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
<b>ACGIH</b>	No components of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.
<b>NTP</b>	No components of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
<b>OSHA</b>	No components of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

### Signs & Symptoms of Exposure

<b>Skin</b>	Irritation.
<b>Eyes</b>	Irritation, watering of eyes, itchiness.
<b>Respiratory</b>	Coughing, baritosis.
<b>Ingestion</b>	Nausea, vomiting.

<b>Chronic Toxicity</b>	Damage to lungs, mucous membranes.
<b>Teratogenicity</b>	Not Available
<b>Mutagenicity</b>	Not Available
<b>Embryotoxicity</b>	Not Available
<b>Specific Target Organ Toxicity</b>	Not Available
<b>Reproductive Toxicity</b>	Not Available
<b>Respiratory/Skin Sensitization</b>	Not Available

---

## 12. ECOLOGICAL INFORMATION

---

### Ecotoxicity

<b>Aquatic Vertebrate</b>	LC50 – Poecilia sp – 59,000 mg/l – 96 hr
<b>Aquatic Invertebrate</b>	EC50 – Daphnia magna – 32mg/l – 48h
<b>Terrestrial</b>	Not Available

<b>Persistence and Degradability</b>	Not Available
<b>Bioaccumulative Potential</b>	Not Available
<b>Mobility in Soil</b>	Not Available
<b>PBT and vPvB Assessment</b>	Not Available
<b>Other Adverse Effects</b>	Not Available

---

### 13. DISPOSAL CONSIDERATIONS

---

<b>Waste Residues</b>	Users should review their operations in terms of the applicable federal/national or local regulations and consult with appropriate regulatory agencies if necessary before disposing of waste product or residues.
<b>Product Containers</b>	Users should review their operations in terms of the applicable federal/national or local regulations and consult with appropriate regulatory agencies if necessary before disposing of waste product containers.

The information offered in section 13 is for the product as shipped. Use and/or alterations to the product may significantly change the characteristics of the material and alter the waste classification and proper disposal methods.

---

### 14. TRANSPORTATION INFORMATION

---

US DOT	Not Dangerous Goods
TDG	Not Dangerous Goods
IMDG	Not Dangerous Goods
Marine Pollutant	No
IATA/ICAO	Not Dangerous Goods

---

### 15. REGULATORY INFORMATION

---

TSCA Inventory Status	All ingredients are listed on the TSCA inventory.
DSCL (EEC)	All ingredients are listed on the DSCL inventory.
California Proposition 65	Not Listed
SARA 302	Not Listed
SARA 304	Not Listed
SARA 311	Barium Sulfate
SARA 312	Barium Sulfate
SARA 313	Not Listed
WHMIS Canada	Not Listed

---

### 16. OTHER INFORMATION

---

Revision	Date
Revision 1	01/08/2013
Revision 2	06/21/2013

Disclaimer: Columbus Chemical Industries, Inc. ("Columbus") believes that the information herein is factual but is not intended to be all inclusive. The information relates only to the specific material designated and does not relate to its use in combination with other materials or its use as to any particular process. Because safety standards and regulations are subject to change and because Columbus has no continuing control over the material, those handling, storing or using the material should satisfy themselves that they have current information regarding the particular way the material is handled, stored or used and that the same is done in accordance with federal, state and local law. COLUMBUS MAKES NO WARRANTY, EXPRESS OR IMPLIED, INCLUDING (WITHOUT LIMITATION) WARRANTIES WITH RESPECT TO THE COMPLETENESS OR CONTINUING ACCURACY OF THE INFORMATION CONTAINED HEREIN OR WITH RESPECT TO FITNESS FOR ANY PARTICULAR USE.